

## PRODUCT SHEET

info@biopac.com support@biopac.com www.biopac.com

## **SS10L PUSHBUTTON HAND SWITCH**

The SS10L pushbutton hand switch is used for remote event marking or for psychophysiological response tests. This easy to hold pushbutton switch is very rugged and reliable, and makes it simple to mark events during recording. When data from the button is displayed on the screen, it normally reads 0 Volts, and when the button is pressed it reads +5 mV.



## **SS10L SPECIFICATIONS**

Cable Length: 2 meters
Connector Type: 9 Pin DIN